

# Transportable Hydrogen Power Generator



### **COSBER GmbH**

Lise-Meitner-Straße 3, 82152 Krailling bei München Germany

Office: +49 (0) 89 2620766-00 Fax: +49 (0) 89 2620766-60 Email: hydrogen@cosber.de

#### **COSBER Production Facility**

8th Floor, Building A, No.28 Dongyang 3rd Road, Danzao Town, Nanhai District, Foshan, Guangdong, China

Office: +86 (0) 757 8661 3098 LinkedIn: Cosber Hydrogen Email: hydrogen@cosber.com www.cosberhea.com






# 300W Fuel Cell System (CSB300)

C@SB=R

CBS300 is a power generation system using air-cooled fuel cells, built-in 48V/10 A lithium-ion battery. It has features of intelligent monitoring, small size, light weight, low noise, and environmental friendly. It can be applied to hydrogen energy two-wheeled vehicles, hydrogen energy mobile power and many other scenarios.






Rated output	300W	
Rated voltage	48V	
Rated current	10A	
Rated voltage range	36~54V	
Max. power output	1440W@30s	
Starting time	<20s@936W	
Overload time	>1min@936W	
Efficiency	≥40%@Rated power	
Duration of system operation	≥2h@400W	
Dimensions	(L×W×H) 276×230×480mm	
Weight	16kg(Oxygen cylinder included)	
Reported data	Equipment online status, hydrogen	
	concentration, location information,	
	lithium-ion SOC, remaining hydrogen	

Air-cooled Fuel Cell



## 3kW Fuel Cell System (CSB3000-M)

CSB-3000-M is an integrated design of a power generation unit and a hydrogen supply unit, each weighs under 40kg. Both units use quick-connect to operate as a complete system rapidly. This system has excellent mobility and reliability. Low noise and green, this system can replace diesel engines for emergency power generation.



Rated output	3kW
Output voltage	43.2~57.6VDC
Starting voltage	48VDC
Power generation efficiency	≥43%
Generating unit dimensions	(L×W×H) 640×330×430mm
Hydrogen supply unit dimensions	(L×W×H) 900×470×440mm
Generating unit weight	38kg
Hydrogen supply unit weight	40kg
Gas bottle volume	28L@35MPa
Hydrogen purity	≥99.99%
Hydrogen consumption	0.7Nm3/kWh
Ambient temperature	-10~40°C
Store temperature	-40~60°C
Altitude	2000m
Noise	≤60dB
Ingress protection	IP44
Communication interface	CAN, RS485






01 02



## 9kW Fuel Cell System (CSB9000)

C@SB=R

The CSB9000 adopts a modular structure design, allowing flexible configuration of different power level stacks, with a maximum configuration of 9kW. It can achieve one-key startup and integrates various power requirements for DC/AC and DC/DC. Compared to traditional diesel engine power, it has advantages such as low noise and environmental friendliness. Compared to battery power, it offers higher energy density and reliability. In scenarios with higher power demands, it can operate in parallel with multiple units.



The hydrogen supply system provides the hydrogen needed for fuel cells, where hydrogen reacts with oxygen from the air inside the fuel cell stack to generate electricity through a chemical reaction. DC/DC and DC/AC converter units convert the variable voltage generated by the fuel cell stack into the voltage required by the load. The main control unit is responsible for signal acquisition, DC/DC output management, alarms, stack protection, communication interfaces, automatic startup, manual startup, and other functions.

Rated output power	9kW
Output voltage	12VDC, 24VDC, 380VAC off-grid
Output frequency	50Hz
Hydrogen inlet pressure	60kPa
Hydrogen conversion efficiency	≥40%
Dimension	(L×W×H) 700×650×1400mm
Weight	≤210kg
Hydrogen purity	≥99.99%
Hydrogen consumption	0.72Nm³/kWh
Operatin temperature	-20~55°C
Storage temperature	-5~55°C
Operating environment humidity	0~95%RH
Ingress protection	IP44
Communication interface	CAN2.0B

Laboratory





## 10kW+ Fuel Cell Systems

Cosber's fuel cell generation products use proton exchange membrane fuel cell technology. The systems are compact with small footprint, and capable of fast-start and shutdown. They are easy to achieve automatic control and unattended, suitable for distributed and centralized power, generation purposes.







DC Output Cabinet

AC output cabinet

**Customized cabinet** 

#### **Product specifications**

Туре	C-FCS-10D	C-FCS-10A	C-FCS-30D	C-FCS-30A	C-FCS-50D	C-FCS-50A
Item	DC Output	AC Output	DC Output	AC Output	DC Output	AC Output
Net output (kW)	10		30		50	
Output mode	Grid connection	on	Grid connecti	on	Grid connection	on
Fuel cell system number/set	1		1		1	
Output pressure (V)	DC40-65V	AC 380V, 50Hz	DC500-700V	AC 380V, 50Hz	DC500-700V	AC 380V, 50Hz
Dimension (L $\times$ W $\times$ H) (m)	0.9x0.8x1.25		1.3x0.9x1.4	2.3x1.3x2.3	1.3x0.9x1.4	2.3x1.3x2.3
Weight (ton)	0.2	0.25	0.5	1.2	0.7	1.5
Efficiency (LHV, Waste heat utilization)	45% - 53%	41% - 48%	49% - 57%	47% - 55%	46% - 57%	44% - 55%
Efficiency (LHV, Self heat dissipation)	44% - 52%	39% - 46%	47% - 57%	46% - 55%	45% - 57%	43% - 55%
Environment temperature (°C)	-10°C to +40°C		-30°C to +45°C		-30°C to +45°C	
Humidity (%RH)	0-95		0-95		0-95	
Start duration (s)	<30		<30		<30	
Low temperature start (min)	<15min @ -10°	C	<15min @ -30	°C	<15min @ -30	°C
Hydrogen inlet presssure (MPa)	0.6-1		1±0.1		1±0.1	
Hydrogen purity	≥99.97%		≥99.97%		≥99.97%	
Hydrogen flow rate (Nm³/h)	<b>≤</b> 9.3		≤22		≤40	
Hydrogen inlet temperature (°C)	€50		€50		€50	
Noise (db)	<b>≤</b> 75		<b>≤</b> 75		<b>≤</b> 75	
Communication	Support CAN, mosbus RTU, modbus TCP					
Power	1kW, AC220V 5kW, AC220V					
Note: Off-grid mode, storage battery, and low hydrogen inlet pressure mode can be configured as needed.						

03 04

Transportable Hydrogen Power Generator

www.cosberhea.com

#### www.cosberhea.com


#### Transportable Hydrogen Power Generator



### **Dual-Pack Metal-Hydrogen Charging Platform**

This system consists of an operational panel, a main water tank cabinet, a chiller, a hydrogen gas detector, etc. Users may assemble the chiller to the main water tank cabinet, and then install the hydrogen gas detector above the main cabinet at a reliable position.

Charging quantity	Two channels
Hydrogen charging pressure	10~25bar
Inlet relief valve start value	200bar
Chiller (accessory)	Temperature control range 5~35°C
Hydrogen gas detector (accessory)	High concentration sound and light alarm
Dimension	(L×W×H) 850×450×750mm



### **Operating environment**

1. The normal operating temperature and humidity range is as follows:

Ambient temperature 0-40°C

Relative humidity 10-95%

Note: The working medium of the accessory chiller is liquid water, so the normal operating temperature of the entire equipment should be above 0°C. In operations below freezing (-20°C and below), the chiller can be omitted, and no liquid water should be injected into the tank.

- 2. For safety considerations, it is prohibited to use this system in small enclosed spaces. It is required to operate in well-ventilated spaces because hydrogen leakage could pose a significant risk. Also, avoid operations near open flames. It is recommended to have portable fire extinguishing equipment such as dry powder and carbon dioxide on-site.
- 3. Hydrogen purity requirements for hydrogen supply equipment:

Туре	Gaseous hydrogen	Bottle pressure not exceeding 150 bar	
Composition	99.99% hydrogen	Purity requirement of 99.99% or higher	
Humidity	Dry gas	No special requirements	
Allowable impurities	Inert gases (nitrogen, oxygen, nitrous oxide, water vapor)	<0.01%	
	Hydrocarbons	<1ppm	
	Oxygen	<220ppm	
	Carbon monoxide and carbon dioxide mixture	<1ppm	
	Sulfides	<0.1ppm	
	Ammonia	<0.05ppm	
	Nitrogen oxides	<0.5ppm	

# Main interface of the dual-pack charging platform software

#### Three major functional modules of the control system

- 1. Electromagnetic valve switch and timing control
- 2. Operation log and exit
- 3. Real-time system data

第气电磁阀 美丽	NO 125	150	60	8 3		
高压-気气电磁阀 美国	2 /2	200-	2 /	80° 90_		
光气时间: 45 min 🛑 🧯	0.0	100%	V° 0.	OOD		
शिरामः 💮 🗓	进气	进气压力		出气压力		
开始充气计时 停止充气	A器明时改量	A路 累计微量	开境温度1	开境温度1		
2023-09-20 14:08:35	NL/min	[]L				
	B路瞬时流量	B路票计微量	开境温度2	开境温度2		
	NL/min					
	H2徐夏1	A路水箱温度1	A路 水箱温度2	AB 水箱温度3		
	D bbur					
	H2徐夏2	B路 水箱温度1	B路 水箱温度2	B路 水稻温度3		
表出	[] ppm	[]]∘c	[] ℃			

### Note

05 06